

GretagMacbeth (XRrite) SpectroEye XRG



Gretag Macbeth (XRrite) SpectroEye XRG A - refurbished - X-Rite Certificate dated from 01.01.2012

Type: SpectroEye
Part No: 36/64/00
DC input: 15 V / 0.8 A

This product has been refurbished and new certified on 16.12.2011.

Default functions:**Measurement functions:**

Density
Dot Gain
Dot Area
Impression Line
Trapping
Remissionsspectrum
Best Match

Special ?E Forms:

?E FMCII
?E CMC
?E* 94 ?E*2000

SpectroEye ® is the worldwide only colour measuring instrument which makes available the rated values for printing after process standard to offset printing (ISO 12647) in the form of spectral data.

Best of all match: It is the only function which "speaks" with the printer. They receive immediately a statement about that with which changes of the layer thickness or colour concentration the given authoritative colour is to be reached. With it becomes the arrangement of the pressure machine so simply as never.

Spectral process standard data: Thanks to these unique data you can work furthermore with the density values, while the passport / Fail-Anzeige refers to the given colour tolerance after process standard offset printing. By these spectral data you can use the «Best of all match» to function also for the setting of the pressure machine after process standard.

Automatic Weisskalibration: To receive optimum measuring results, the white reference is inserted in SpectroEye. The calibration is explained automatically without influencing control of the user.

Positioning independent of direction: To guarantee a positioning independent of direction of the measuring instrument, is equipped SpectroEye with a ring lighting. This is especially important with measurements on unpainted substrates.

High-resolution measuring system: With the internal spectral resolution of 3.3 nm grasps SpectroEye also the smallest colour divergences.

Order-oriented work: In SpectroEye orders can be put on, so that measuring rows can be automatically grasped and be assigned to the respective reference. Besides, orders of the PC can be loaded with the software Color Quality™ in SpectroEye and from SpectroEye for the other evaluation and documentation in the PC.

Access to the digital Pan tone ® to colour fields: All 1114 colours on painted, unpainted and matt paper contain the SpectroEye Pan tone of fields. Furthermore the integration of the colour fields HKS, Toyo and DIC is possible.

Certificate to her SpectroEye even with NetProfiler 2: The NetProfiler exists of software and a Kalibrierkarte especially developed for the pressure industry. Via Internet the measured values are compared to the deposited defaults and a correction profile is calculated that can be loaded by the NetProfiler software directly in SpectroEye.

Measuring results with NetProfiler 2:

exact communication between several devices of the same type
if the measuring quality and reliability of the devices receives
if the availability of the devices receives longer by the lengthening from service intervals

Measuring technology:

Spectral measurement holografisches declension grid
Spectral range from 380nm to 730nm
Measuring value issue 10nm (internal resolution 3.3nm)
Measuring mode Remission
Measuring geometry 45 °/0 ° ring optics, German Institute for Standardization 5033
Measuring screen Ø 4.5 mm
Source of light Wolfram, gas-filled, light kind A
Physical filtering neutrally, approximated electric light bulb light A
polarises
approximated daylight D65
especially on inquiry also UV suppression
Measuring time without filter: approx. 2see
Polarisation filter: approx. 3see
D65 filter: approx. 2see
Measuring area density to German Institute for Standardization 16536: From 0.00D to 2.5D
Linearity $\pm 0,01D$
Short-term ability for reproduction 0.02 deltas E^* CIELAB (D50, 2 °), average from 10 measurements in the distance of 10 seconds on white
Density ability for reproduction Density German Institute for Standardization 16536 (ability for reproduction $\pm 0,01D$):
No filter 0.0D - 2.5D, Yellow 0.0D - 2.0D
Pole filter 0.0D - 2.2D, Yellow 0.0D - 1.8D
Measuring head extendably
Filter wheel motor powered
Absolutweißkalibration automatically on integrated white reference
Device examination automatic examination of the spectral Kalibration
Thick filter allocation by hand and automatically
Average education Mittelung about several measuring values
Measuring value allocation manual and automatic allocation of the tests to the references

Measuring terms:

White relation absolutely, relatively
Light kinds of the colour metrics D50, D65, A, C, D30... D300, F1... F12, user-defined
Normal observer's corner 2 °, 10 °
Density norm German Institute for Standardization 16536, German Institute for Standardization 16536 NB, STATUS ANSI A, STATUS ANSI T, ISO status I (SPI), user-defined

Measuring functions:

Colour systems standard: CIE $L^*a^*b^*$, CIE $L^*C^*h^*$ (a^*b^*), delta E CIELAB, delta E* 94
optionally: CIE XYZ, CIE xyY, CIE $L^*u^*v^*$, CIE $L^*C^*h^*$ (u^*v^*), LABmg, LCHmg, Hunter Lab, RxRyRz
Colour distance formulae optionally: Delta E* CIELUV, delta E CMC, delta E FMCII, delta E mg, delta E Hunter Lab, Metamerieindex
Densitometrie standard: Density, sound value increase, surface cover, colour acceptance
optionally: all thick, pressure identity line, pressure plate, contrast, tone mistake, Verschwärzlichung, autofunction
Colour strength optionally: absolutely (K/S) and relatively (DS)

White degrees and yellow degrees optionally: White degree CIE, white degree ASTM E313, white degree Berger, white degree Stensby, ISO brightness R457, yellow degree ASTM E313, yellow degree ASTM D1925, tone divergence number CIE

Special function Best of all match

Colour fields optionally: To PAN TONE Color Formula guide; finder TOYO Color; guide DIC Color; HKS E, K, N and Z

Data protection function optionally: Settings protect, multiple user

Interfaces:

Data socket RJ45 link

serial interface RS 232C with from 300 to 57600 Baud

Ethernet 10 BaseT, 10 MByte / p.

Electricity supply:

Electricity supply NiMH accumulator, nom. 7.2 V, 1300mAh

Mains appliance specification 85 VAC to 270 VAC, 47 hertz to 63 hertz

Loading time approx. 3h, automatic disconnection

Loading state automatic control and announcement of the capacity

Measurements per load approx. in 3000

Mechanical data:

Dimensions length: 24.5 cm, width: 8.3 cm, height: 8 cm

Weight approx. 990 g

Qualities

Ideal measuring instrument for the pressure hall for all colour measurements and thick measurements

Quick arrangement of the pressure machine with spectral data for PSO, BMW, ECP

Clear representation of the measuring values by highly dissolving display

Measurement independent of direction by 45 °/0 °-ring optics (circular lighting)

Exact positioning by automatically extendable measuring head

Enlargement of the functional extent by free switch code any time possibly

Exact communication about Pan tone and HKS* by integrated digital ones

Colour fields (* additional option, can be switched at the owner's expense freely)

With 4.5 mm or 3.2 mm (SATURDAY – Small Aperture) measuring screen available.

Devices also with additional UV cut filter available.

Technical data

Measuring geometry: 45 °/0 °-ring optics (circular lighting)

Source of light: gas-filled wolfram lamp, light kind A

Screen diameter: 4.5 mm or 3.2 mm (not interchangeable)

Measuring area: 380 nm - 730 nm, reflexion from 0 to 200%, density 0 – 2.5 D

Spectral resolution: Inside: 3.3 nm, issue: 10 nm

Device divergence: middle $\Delta E_{ab} \leq 0.3$ (more than 12 tiles BCRA)

Wiederholgenauigkeit: max. $\Delta E_{ab} = 0.02$ (on white ceramics), density 0.01 D

Physical filters: No, pole, D65; optionally: UV cut (everybody automatically changeable)

Announcement: Graphic display 128 x 256 pixels

Storage space: 2000 measuring values all together

Interface: serial: RS-232C; USB about adaptor

Electricity supply: NiMH (Nickel-Metal-Hydrid) accumulator

BRAKENSIEK®
SYSTEMHAUS



Please only contact us via our registration form and only if you are a business person yourself. Every offer is subject to prior sale and includes your acceptance to our terms & conditions [Terms and conditions \(AGB\)](#). All logos and trademarks on this site are the property of their respective owners.

You will always receive an invoice including tax, which can be paid via wire transfer, in advance or cash. If you register on paypal, you may also pay by charging your paypal account with your credit card. If you are an EU member and you have a validated tax number which can be validated here: [VIES VAT number validation / MwSt.-Informationsaustauschsystem MIAS\) Validierung der MwSt.-Nummer](#) then you pay tax-free. If you are from outside the EU, you can only pay tax-free, if the export is done with the transport company, called 'Schenker'. If you are not using 'Schenker', we cannot guarantee that we will get the export confirmation in time. In that case, you have to pay tax and you get it.

Mitglied der

**Brakensiek Systemhaus
GmbH & Co. KG**
Klönnestraße 94
D-44143 Dortmund**BRAKENSIEK®**
SYSTEMHAUS

Mitglied im

**www.brakensiek.com****Tim Brakensiek**

Mitglied des

 **+49(0)231.985-00 10**

Premium Partner

 **+49(0)231.985-2000**